

PREMIUM OUT OF BED  
CUSHION MAT

STRONG, SECURE  
ELECTRICAL  
CONNECTIVITY

THICK FIRM FOAM TO  
REDUCE, IF NOT  
ELIMINATE INJURIES

INCLUDES A 2-PIECE  
SENSOR MAT AND A  
WIRELESS  
TRANSMITTER

NO MORE CORDS  
BETWEEN THE SENSOR  
MAT, THE RESIDENT &  
THE CALLPOINT

FOLDABLE FOR EASY  
STORAGE

EASY TO MOVE FROM  
ROOM TO ROOM

SPRAY AND WIPE TO  
CLEAN WITH ANTI-  
BACTERIA SOLVENT

INTEGRATES TO MOST  
NURSE CALL SYSTEMS

PLUG & PLAY  
OPERATION

# Cushion Floor Sensor Mat Cordless 6.3mm Connection

TGA Registered ID 223902  
RCM Approved  
AS/NZS 61000.6.3.2012



## PRODUCT CODES:

**Cushion Floor Mat (6.3mm) & USB Transmitter (6.3mm): MED-FM-04X-WT**

**FULL KIT: Receiver Box, Floor Mat & Transmitter: MED-FM-04K-W6T(X)/W3T(X)**

Indigo Care provides a smart Australian designed Foldable Premium Cordless Cushion “Crash” Sensor Mat with a 6.3mm connection that is specifically designed to be used with our Transmitter (RTU-FM), and that will immediately alert staff when a resident steps on the sensor mat. The Cushion sensor mat is purposely designed for easier storage and trip-hazard free. The 6.3mm plug provides a secure electrical connection that increases the sensor mat’s strength and durability whilst extending its lifespan.

The transmitter is an exclusive ID encoded RF Transmitter which communicates with the Cordless Receiver (RRU) or the Universal Call Point (UCPV5.1). It allows the Cushion Floor mat to wirelessly transmit an alarm to the call point.

Simply connect the Transmitter to the cushion floor sensor mat and program it to the RRU or Dual Function Call Point by following the instructions printed on the Receiver. The cushion sensor mat will now trigger the call point when activated within the transmitting area.

*(Note: USB Transmitter and USB Cushion Floor Sensor Mat can be ordered separately).*

## KEY SPECIFICATIONS:

### Floor mat

- **Dimensions: 1800mm X 750mm X 40mm (Foldable)**
- **Electrical Resistance < 150 Ohm**
- **Blue PVC Soft Foam Design**
- **40mm of Foam Padding**
- **Connection : 6.3mm**

### Transmitter

- **Box Dimensions: 50 x 35 x 14mm**
- **Connection: 6.3mm**
- **No External Antenna**
- **LED low battery indicator**
- **Transmits up to 25m (line of sight)**
- **Frequency: 433.92MHz**
- **Uses a 3V battery-CR2032**
- **Warranty: 12 months**

## CORDLESS RANGE:

- **Cordless Receiver (RRU)**
- **Cordless Transmitter (RTU)**
- **Cordless Under Mattress Sensor Mat**
- **Cordless Floor Sensor Mat**
- **Cordless Bed Sensor Mat**
- **Cordless Chair Mat**
- **Cordless Waterproof Neck Pendant**
- **Cordless Waterproof Wrist Pendant**
- **Cordless PIR Motion Sensor**
- **Cordless Suspense Point**
- **Cordless Doorway Sensor**

## INDIGO CARE

(Horizon Electronics Company, T/as)  
2/93 Rushdale Street, Knoxfield, VIC, 3180  
PH +61 3 9763-2988  
[www.horizone.com.au](http://www.horizone.com.au)  
ABN 36007302801

## ORDER INFORMATION

Email your purchase orders to  
[sales@indigocare.com.au](mailto:sales@indigocare.com.au)

